

Diversey

J-Fill®
QuattroSelect®
Dispensing
System



Wall-mounted system dispenses four different J-Fill® products into bottles, buckets and floor care machines.

Features

- The J-Fill platform is a close-looped system which virtually eliminates contact with chemical concentrates
- Rugged powder coated steel construction with lockable cabinet doors (comes with keys)
- Product identification windows
- Built with one handed 1.5 GPM low flow and low foam bottle fill
- 8' 3.1 GPM high flow bucket fill hose with easy to use point of use activation
- Smartvalve™/MC technology automatically chooses correct flow rate in one operation
- Meets ASSE 1055-B back-flow prevention requirements
- SafeGap™/MC and Air Gap eductors meets ASSE 1055B standard for back flow prevention *
- Air Gap backflow prevention
- Design only allows J-Fill packaging to be used within dispenser

Benefits

- Uses super-concentrated and hyper-concentrated chemicals, reduces "in-use" cost and solid waste disposal
- Power coated steel doors resist corrosion and are easy to clean
- Uses J-Fill Spill-Tite™/MC cartridges which are leak proof and virtually eliminates chemical exposure, tampering and manually diluting products
- Metering tip in each J-Fill® cartridge ensures precise dilution ratios
- Drip tray with drain hose
- Remote high flow bucket/autoscrubber fill gun
- One handed low flow bottle filling

Applications

- Wall mounted four product chemical dispenser
- For filling bottles, buckets, or floor care machines
- For use in schools, office buildings, foodservice, hospitality, industrial, retail stores and health care facilities

J-Fill® QuattroSelect® Dispensing System



Description of Features

QuattroSelect Dispensing System allows you to choose from four different products with the turn of a dial. Simply select the product you desire, choose one handed low flow bottle fill or point of use bucket activation and dispense ready-to-use solutions into spray bottles, buckets and automatic scrubbers. The lockable cabinet helps eliminate unwanted cartridge removal.

* Check local plumbing regulations for proper installation and back flow protection requirements

Product Specifications

Description	
Unit Dimensions	24.25" x 18.5" x 7.5" (62 cm x 47 cm x 19 cm)
Weight	15 lbs./6.8 kg
Weight in Carton	19 lbs./8.6 kg
Carton Dimension	27" x 20.5" x 9.7" (68 cm x 52.1 cm x 24.13 cm)
Low Flow Rate	1.5 gpm (5.1 Lpm)
High Flow Rate	4.0 gpm (15.0 Lpm)
Water In-Let Hose	4' (1.22 m)
Remote Bucket Fill Hose	8' (2.44 m)
Drip Tray Drainage Hose	8' (2.44 m)

Available Items

Product Code	Description/Package Size
D3764735	J-Fill® QuattroSelect® Air Gap Dispenser / 1 Unit
D3754220	J-Fill® QuattroSelect® Safe Gap Dispenser / 1 Unit
D5913247	J-Fill® QuattroSelect® Safe Gap dispenser - Solid Door Unit / 1 Unit

Operating Range Requirements

Description	Concentrate
Water Pressure	30–85 psi (170–580 KPA)
Water Flow	> 2.0 gpm
Water Temperature	40–120° F (5–48° C)

ASSE 1055-B backflow prevention requirements.

Safety Reminder

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use, and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDSs are available on-line at www.sealedair.com or by calling 888-352-2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate. Please refer to the Diversey HazMat Library, only available through Internet Explorer, <http://naextranet.diversey.com/dot/>, for up to date shipping information.