



## TK-FINE VARIO L PENCIL



- TK-Fine Vario L Pencils are available in 0.35mm, 0.5mm, 0.7mm and 1.0mm and come equipped with 3 (HB) leads.
- Soft/hard mechanism "soft": the lead is cushioned for writing "hard": the lead is held rigid for drawing.
- Metal grip zone with adjustable window to change degree of lead hardness if desired.

1. Remove the eraser holder (3) from the barrel (2) by firmly pulling the eraser holder (3) out.
2. Insert new Faber-Castell leads (4) into the back end of the barrel (2). Add no more than 5 leads.  
If more leads are used this may cause a jam.
3. Return the eraser holder (3) to the barrel (2) by firmly pushing the eraser holder (3) back into place.
4. To advance the lead, push down on the eraser holder (3) and begin writing.
5. To retract the lead, push down on the eraser holder (3) push the lead back into the front piece (1) while the eraser holder (3) is held in place.

REFILLS Eraser: #131596 on Blister Card  
Lead degrees of hardness available: 0.35mm B, HB, H, 2H  
0.5mm 2B, B, HB, F, H, 2H, 3H  
0.7mm 2B, B, HB, H, 2H  
1.0mm HB, B, 2B