INVACARE® PLATINUM™ 10 OXYGEN CONCENTRATOR





The Invacare® Platinum™ 10 Oxygen Concentrator designed to provide an alternative to liquid systems and is known for reliability and performance. The 10 liter unit features quiet operation, a top handle and bottom recesses for easy handling and a side filter access door. In addition, the concentrator is compatible with the Invacare® HomeFill® Oxygen System and is available with an Invacare® SensO2® Oxygen Purity Sensor.

Features

Pressure-based system is superior to timing-based systems

Self diagnostic electronics designed to minimize troubleshooting time

Top handle for ease of mobility

Battery-free power loss alarm, Invacare® Sieve-GARD™ Monitor protects sieve from degradation, compressor 35 psi pressure-relief valve and low flow alarm

Provider Benefits

Designed to provide continuous flow up to 10 liters per minute as an alternative to liquid systems

All Platinum 10 stationary concentrators include a HomeFill system port for inventory flexibility

Patient-accessible reset button helps minimize emergency service calls

Patient Benefits

User friendly design with easy to see control panel, humidifier bottle holder and filter access

HomeFill system compatibility allows patients with flow rates up to 5LPM to enjoy life's experiences with small, refillable cylinders

Reliable concentrator provides unlimited, worry-free oxygen supply

HCPCS Code: E1390







- 1. Invacare® HomeFill® Oxygen System connection
- 2. Easy to maintain filter

Model#

IRC10LX

IRC10LXO2

3. Also available with Invacare® SensO2® Oxygen Purity Sensor



Dimensions Weight Shipping Quantity Oxygen Flow Maximum Pressure Relief Weight Flow Range Outlet Pressure Mechanism 26 ³/₈" H 54 lb. 60 lb. 1 Per Case 10 LPM 2-10 LPM 9+/- 0.5 PSI 35 PSI 18 3/8" W 18 Per Pallet +/- 3.5 PSI 14 ³/₈" D



Oxygen

Purity

94%-87%



Filter



Electrical

Requirements

120 VAC



Rated

5.2 A







Sound Limited Average Power Consumption Warranty Current Input Level 550 W 58 db (A) 3 Years

Cabinet At All Flow Compressor Inlet, +/- 10%, 60 Hz Rates Outlet HEPA (132VAC/108VAC)

All references to HCPCS codes: Providers are responsible for determining the appropriate billing codes when submitting claims to the Medicare program, and should consult an attorney or other advisor to discuss specific situations in further detail.

Invacare Corporation

www.invacare.com

USA

One Invacare Way Elyria, Ohio 44035-4190 (800) 333-6900

Canada

570 Matheson Blvd. E., Unit 8 Mississauga, Ontario L4Z 4G4 Canada (800) 668 - 5324

©2017 Invacare Corporation. All rights reserved. Trademarks are identified by the symbols ™ and ®. All trademarks are owned by or licensed to Invacare Corporation unless otherwise noted. Specifications are subject to change without notification. Form No. 11-190 Rev. 06/17 170582

