

bright starts™

Oball Classic™
Easy-Grasp Toy

オーボール クラシック

0M+ 対象年齢: 0カ月以上

The original easy-grasp
oball™
Technology

Crawling™
ハイハイの
ころに

Fine Motor™
手指を
動かそう

UPC here 80%

CE UK CA

DONNEZ OU RECYCLEZ ASSOCIATION OU MAGASIN DÉCHÈTERIE
Adresses sur quefairedemesdechets.fr

ASTM F963

振ったり、転がしたり。やわらかくて、にぎりやすいボール

注意

保護者の方へ 必ずお読みください。

- ご使用の際は、必ず保護者の方が付き添い、危険な使い方をしないよう注意してください。
- 安全のため、破損・変形したおもちゃは使用しないでください。
- 小さな部品が取れてしまった場合、速やかに処分してください。

〈取扱上の注意〉

- ご使用前およびお手入れは、中性洗剤をうすめた水または清潔な水で絞った布で拭き自然乾燥させてください。漂白剤、アンモニア、アルコールを含むクリーナーは製品にダメージを与える場合がありますので使用しないでください。
- 煮沸消毒はしないでください。
- 次亜塩素酸ナトリウムを含む哺乳瓶殺菌剤等を使用しないでください。
- パッケージは、小さなお子様の手の届かない所に保管し、必要に応じてご参照ください。
- 梱包資材は玩具ではありません。全てを取り外してからお子様にお与えください。

EN CLEANING INSTRUCTIONS: Clean before use with a damp cloth and mild soap. Air dry. Cleaners containing bleach, ammonia, or alcohol can damage the product. IMPORTANT: Remove all packaging and fasteners before giving product to child. Retain this package for future reference. It contains important information. For single family use only.

MANUFACTURED FOR **kids2™ kids II®** ©2026 KIDS2, LLC
KIDS2, LLC ATLANTA, GA USA 30305 • 1-800-230-8190 • www.kids2.com/help

製造元/お問合わせ先: **Kids2 Japan 株式会社**
〒150-0013 東京都渋谷区恵比寿4-3-5-704
TEL.03(5322)6081 www.kids2.com/contact-jp

※パッケージの写真と実際の商品は異なる場合がございます。

■主な材質/ポリウレタン

brightstarts.com

UPC here 80%
PROOF OF PURCHASE • PREUVE D'ACHAT
12288-JP • Bright Starts • PL021426
MADE IN CHINA

Short
UPC EXAMPLE

1.125"

0.25"

FOR REFERENCE ONLY

0 074451 118034

kids2™

File Name: 12288_JP_PL021426
Brand: Bright Starts_Oball
Category: Peg
Product Name: Oball Classic
Package Designer: Nureen/Nico
Product Manager: .
Engineer:
Languages: Languages on Package 2L
Dimensions: 5.625"Wx4"H

Packaging Prints
CMYK

Cyan
Magenta
Yellow
Black

pressSIGN CMYK_Colourbar_ISO 12647-2 Coated White Backing v6_labels_below i1Pro Contrast Bars.eps

pressSIGN CMYK_Colourbar_ISO 12647-2 Coated White Backing v6_labels_below.eps

There are two color bars on this proof and in the art file. One to be used with X-rite I1 Pro Spectrophotometer. The other can be used with most other spectrophotometers. Printers must repeat one of the two color bars all the way across the width (grripper edge) of the press sheets on sample runs and production runs. Failure to comply will result in the remaking of film and/or plates at your cost. 数码稿以及设计文件包含了两种色带。一种适用于X-rite (爱色丽) I1 Pro 分光光度计, 另一种适用于其它大部分的分光光度计。在打样或者批量生产时, 印刷厂必须选择其中一种色带并重复添加直到覆盖整张纸的宽度(叼口边)。没有按照上述要求而导致重新出菲林、出版的费用将由印刷厂承担。