

Standard POP  
Size: 5.5" X 7.25"

<p><b>kids</b>™</p> <p><b>File Name:</b> 17501_8L_STDPOP123124  <b>Brand:</b> Bright Starts - Disney  <b>Category:</b> Bouncer  <b>Product Name:</b> Stitch Bouncer  <b>Package Designer:</b> Nureen/Nico  <b>Product Manager:</b> Erica V  <b>Engineer:</b> Enter Name  <b>Languages:</b> Languages on Package 3/8  <b>Dimensions:</b> see die line</p>	<p><b>Packaging Prints</b>  PMS 3248C plus CMYK  L*75.63 a*-32.76 b*-2.9</p> <table border="1"> <tr> <td>100%</td><td>75%</td><td>50%</td><td>25%</td><td>10%</td><td>3%</td><td>2%</td><td>1%</td><td>Color</td> </tr> <tr> <td colspan="8">PMS 3248 C</td> </tr> <tr> <td colspan="8">Cyan</td> </tr> <tr> <td colspan="8">Magenta</td> </tr> <tr> <td colspan="8">Yellow</td> </tr> <tr> <td colspan="8">Black</td> </tr> </table>	100%	75%	50%	25%	10%	3%	2%	1%	Color	PMS 3248 C								Cyan								Magenta								Yellow								Black								<p>pressSIGN CMYK 1 Spot_Colourbar_ISO 12647-2 Coated White Backing v6_labels_below i1Pro Contrast Bars.eps</p> <p>pressSIGN CMYK 1 Spot_Colourbar_ISO 12647-2 Coated White Backing v6_labels_below.eps</p>
100%	75%	50%	25%	10%	3%	2%	1%	Color																																											
PMS 3248 C																																																			
Cyan																																																			
Magenta																																																			
Yellow																																																			
Black																																																			

There are two color bars on this proof and in the art file. One to be used with X-rite I1 Pro Spectrophotometer. The other can be used with most other spectrophotometers. Printers must repeat one of the two color bars all the way across the width (gripper edge) of the press sheets on sample runs and production runs. Failure to comply will result in the remaking of film and/or plates at your cost. 数码稿以及设计文件包含了两种色带。一种适用于X-rite (爱色丽) I1 Pro 分光光度计, 另一种适用于其它大部分的分光光度计。在打样或者批量生产时, 印刷厂必须选择其中一种色带并重复添加直到覆盖整张纸的宽度(叼口边)。没有按照上述要求而导致重新出菲林、出版的费用将由印刷厂承担。

# Standard POP Attachment Instructions



Attach to seat pad seam  
in the position shown above  
with 2 swift tacks  
9mm swift tacks