

MANUFACTURED FOR: HARBORLY PAPER, LLC © 2025 KIDS2, LLC www.kids2.com/tp

KIDS2, LLC ATLANTA, GA USA 30305 • 1-800-230-8100

IMPORTED BY: IMPORTER PAK

KIDS2 CANADA CO. PO BOX 50559, 8881 LAWRENCE PLAZA, TORONTO, ON, M3A 3B7

KIDS2 AUSTRALIA PTY LIMITED CASTLE HILL, NSW AUSTRALIA 2154 • (02) 8994-1855

KIDS2 JAPAN 株式会社 東京都中央区銀座 4-3-5/104 03153226081

KIDS2 UK LTD, GROUND FLOOR, SUITE 41A, BRICKS&PEBBLES PARK, BRACKENHEATH WAY, HEATH, HEATHFIELD, HP22 4TZ • +44 01582 816 080

KIDS2 EUROPE BV & ZIEVEN, KEZESGÖMÖCH 207, 1016 ED AMSTERDAM, NETHERLANDS • +31 20 2470934

KIDS2 US MEXICO S.A. DE C.V., AVENIDA VASCO DE QUROGA NO. 871, 3300, NO. INT. 505 A, COL. LOMAS DE SANTA FE, ALVARO OBREGON, CIUDAD DE MEXICO, MEXICO, C.P. 07179, MEXICO • KIN000027017 • (52) 5292-8408

MADE IN CHINA • HECHO EN CHINA • FABRIQUE EN CHINE

Printed in Mexico by Harborly Paper, LLC. © 2025 Harborly Paper, LLC. All rights reserved. Printed in Mexico by Harborly Paper, LLC. © 2025 Harborly Paper, LLC. All rights reserved.

PROOF OF PURCHASE - PREUVE D'ACHAT 17064-172 - SwaddleMe - PL1112525

LEARN MORE ABOUT STAGE 3 IN OUR STAGES OF HEALTHY SLEEP

MÁS INFORMACIÓN SOBRE LA 3ª ETAPA EN NUESTRAS ETAPAS DEL SUEÑO SALUDABLE

« ÉTAPES POUR UN SOMMEIL SAIN »

stage/etapa/étape

1 2 3

QR Code

Room Temperatures / Températures des Habitacions	1.0-1.5 TOG	2.0-3.0 TOG
72° - 75°F (22° - 24°C)	3M	3M
68° - 72°F (20° - 22°C)	3M	3M
64° - 68°F (18° - 20°C)	3M	3M
61° - 64°F (16° - 18°C)	3M	3M

Room Temperatures / Températures des Habitacions

1.0-1.5 TOG

2.0-3.0 TOG

0M 3M 6M 18M

1 Swaddle Ready™ Start with Arms-in™ Sleep for Comfort™

2 Rolling Ready™ Arms-Free Sleep with Confidence™

3 Ready to Move™ Grow into Arms-Free Sleep with Peace of Mind™

0-3M 3-6M 6-18M

Safety in Every Stage™

by ingenuity

swaddleme™

UPC here 80%

stage/etapa/étape 1 2 3

Healthy sleep starts here.™

UPC here 80%

swaddleme™ by ingenuity

stage/etapa/étape 1 2 3

100% cotton / 100% algodón / 100% coton

UPC here 80%

swaddleme™ by ingenuity

Night Sack Sleeper / Saco de Dormir / Sac de Couchage / 1-pack/paquete/paquet

3 Ready to Move™

EASY TO USE / FÁCIL DE USAR / FACILE À UTILISER

1 2 3

#1 SWADDLE MANUFACTURER™

Designed to replace loose blankets in crib / Diseñado para sustituir las mantas sueltas en la cuna / Conçu pour remplacer les couvertures lâches dans les berceaux

Wearable design for healthy sleep / Diseño fácil de poner para un sueño saludable / Conception portable pour un bon sommeil

Easy Change™ zipper / Easy Change™ zipper / fermeture à glissière

Hip-healthy design / Diseño de corte holgado en la cadera / Conception saine pour les hanches

3-18M / 14-24 lbs (6.4-10.9 kg) / Up to / Jusqu'à / Hasta: 25.6-31.5 in (65-80 cm)

TOG 1.0

Oeko Tex Standard 100 / BI 030, 192607 / TESTEX

Night Sack Sleeper / Saco de Dormir / Sac de Couchage / 1-pack/paquete/paquet

QR Code

UPC here 80%

PROOF OF PURCHASE - PREUVE D'ACHAT 17064-172 - SwaddleMe - PL112525

EN: WARNING! Do not use if the child can climb out of the cot. WARNING! Do not use in combination with other bedding items (e.g. cot duvet). Baby should be lightly clothed and sleep at a room temperature of 16.7-22 deg C (62-72 deg F). Baby should not feel hot to the touch. Place infants on their back to sleep unless otherwise advised by a physician. Do not allow fabric to cover nose or mouth. Please retain information for future reference. Colors and styles may vary. CONTENTS: 100% cotton inclusion of decoration CARE INSTRUCTIONS: Wash before first use. Machine wash cold, gentle cycle with like colors. Use non-chlorine bleach only if needed. Tumble dry, low heat or line dry. Do not iron. Do not dry clean.

ES: ADVERTENCIA! No utilizar cuando el bebé pueda salir de la cuna por sí mismo. ADVERTENCIA! No utilizar junto con ropa de cama adicional (por ejemplo, edredón de cama). El bebé debe estar ligeramente vestido y dormir a una temperatura ambiente de 16.7 - 22 °C (62 - 72 °F). El bebé no debe sentirse caliente al tacto. Recostar a los bebés boca arriba para dormir, a menos que un médico indique lo contrario. No dejar que la tela cubra la nariz ni la boca. Conservar la información para futuras consultas. Los colores y estilos pueden variar. CONTENIDO: 100% algodón sin detalles decorativos INSTRUCCIONES DE CUIDADO: Lavar antes del primer uso. Lavar a máquina en frío, ciclo delicado con colores similares. Usar lejía sin cloro sólo si es necesario. Secar en secadora a baja temperatura o al aire libre. No planchar. No limpiar en seco.

FR: AVERTISSEMENT! Ne pas utiliser quand l'enfant a appris à sortir du lit. AVERTISSEMENT! Ne pas utiliser avec d'autres draps (ie. duvet). Bébé ne doit pas être trop couvert et dormir à une température comprise entre 16,7-22 deg C (62-72 deg F). Au toucher, bébé ne doit pas avoir semblé avoir trop chaud. Placez les nourissons sur le dos pour dormir, sauf avis contraire d'un médecin. Ne pas laisser le tissu couvrir le nez ou la bouche. Conservez notices pour futures références. Couleurs et motifs peuvent être différents du modèle. AVEC: coton 100% sauf pour les motifs. INSTRUCTIONS D'ENTRETIEN: Laver avant la première utilisation et fermer les trois poignets avant le lavage. Utiliser de l'eau de javel sans chlore uniquement si nécessaire. Sécher par séchage à basse température ou en ligne. Ne pas repasser. Ne pas nettoyer à sec.

UPC here 80%

PROOF OF PURCHASE - PREUVE D'ACHAT 17064-172 - SwaddleMe - PL112525

KIDS2™

File Name: 17064-172_3L_PL112525

Brand: SwaddleMe

Category: Swaddle

Product Name: SwaddleMe Sleeper

Artist Dot

Package Designer: Patrick Rice

Product Manager: Enter Name

Engineer: Enter Name

Languages: Languages on Package 3

Dimensions: see dieline

Packaging Prints

PMS 353 C plus CMYK

L*81.64 a*39.47 b*14.56

PMS 353 C

Cyan

Magenta

Yellow

Black

PRINTING INSTRUCTIONS

PRINTING INSTRUCTIONS

pressSIGN CMYK 1 Spot_Colourbar_ISO 12647-2 Coated White Backing v6_Labels_below i1Pro Contrast Bars.aps

pressSIGN CMYK 1 Spot_Colourbar_ISO 12647-2 Coated White Backing v6_Labels_below.aps

Short UPC EXAMPLE

1.125"

FOR REFERENCE ONLY

0 074451 118034

There are two color bars on this proof and in the art file. One to be used with X-rite I1 Pro Spectrophotometer. The other can be used with most other spectrophotometers. Printers must repeat one of the two color bars all the way across the width (grripper edge) of the press sheets on sample runs and production runs. Failure to comply will result in the remaking of film and/or plates at your cost. 数码稿以及设计文件包含两个颜色条。一种适用于X-rite (爱色丽) I1 Pro 分光光度计，另一种适用于其它大部分的分光光度计。在打样或者批量生产时，印刷厂必须选择其中一种色带并重复添加直到覆盖整张纸的宽度(印口边)。没有按照上述要求导致重新出菲林、出版的費用将由印刷厂承担。