



16989



Features of a full size high chair but with a slender fold
 Características de una trona de tamaño normal pero con un plegado estilizado
 Caractéristiques d'une chaise haute de taille normale mais avec un pliage plus fin



3-section Twist & Dine™ plate locks securely in place
 El plato Twist & Dine™ de 3 secciones se bloquea firmemente en su sitio
 La plaque Twist & Dine™ à 3 sections se verrouille solidement en place

ingenuitybaby.com



Features of a full size high chair but with a slender fold
 Características de una trona de tamaño normal pero con un plegado estilizado
 Caractéristiques d'une chaise haute de taille normale mais avec un pliage plus fin

3-section Twist & Dine™ plate locks securely in place
 El plato Twist & Dine™ de 3 secciones se bloquea firmemente en su sitio
 La plaque Twist & Dine™ à 3 sections se verrouille solidement en place



Slender fold, lightweight design is easy to move
 Plegado fino, diseño ligero fácil de mover
 Pliage fin, conception légère, facile à déplacer

ingenuitybaby.com



Features of a full size high chair but with a slender fold
 Características de una trona de tamaño normal pero con un plegado estilizado
 Caractéristiques d'une chaise haute de taille normale mais avec un pliage plus fin



3-section Twist & Dine™ plate locks securely in place
 El plato Twist & Dine™ de 3 secciones se bloquea firmemente en su sitio
 La plaque Twist & Dine™ à 3 sections se verrouille solidement en place

ingenuitybaby.com



kids2™

File Name: 16989_WS_ST07225
 Brand: Ingenuity
 Category: High Chair
 Product Name: Compact Folding High Chair
 Package Designer: alisa
 Product Manager: Enter Name
 Engineer: Enter Name
 Language: 3L (EN, ES, FR)
 Dimensions:

Packaging Prints
 PMS 353 C plus CMYK
 L:91 64.4° 59.47 5°14.56

pressSIGN CMYK 1 Spot_Colourbar_ISO 12647-2 Coated White Backing v6_labels_below iPro Contrast Bars.aps

pressSIGN CMYK 1 Spot_Colourbar_ISO 12647-2 Coated White Backing v6_labels_below.aps

CMYK
 Cyan
 Magenta
 Yellow
 Black

PMS 353 C
 Cyan
 Magenta
 Yellow
 Black

There are two color bars on this proof and in the art file. One to be used with X-rite D50 Spectrophotometer. The other can be used with most other spectrophotometers.
 Printers must repeat one of the two color bars all the way across the width (grasper edge) of the press sheets on sample runs and production runs. Failure to comply will result in the remaking of film and/or plates at your cost.
 必须重复以上两个色条直到横贯出纸幅。出错的数据将导致印刷失败。