





Innovative Designs Inspiring Change.

Wire Event **Container**[™] Series

Green Your Event

Product Data Sheet | Version 1.5







View the Wire Event Container™ Series Online!











Green Your Event

The Wire Event Container™ offers a simple solution to a complex problem - effective refuse collection at an event! These containers were designed for easy set-up and removal with metal stands that can easily be stacked and are magnetic to the lid which helps keep the bag and container in place when in use. Clearly identify streams with labels, colored lids and multiple opening options to achieve optimal waste diversion at your next event!adaptable, multi-stream design of the Wire Event Container™ has been expertly designed to complement and shift with your program.



Some components are made from 100% post-consumer recycled content

POPULAR SKU'S









www.buschsystems.com • 1.800.565.9931 • 81 Rawson Avenue, Barrie, Ontario, Canada L4N 6E5



BUILD YOUR WIRE EVENT CONTAINER™ STATION











+



ONE: THE BODY

• 32 Gallons (30" High)

TWO: THE LID

 See lid opening specifications for available openings THREE: THE LABEL

 Choose from our stock options or customize your own! FOUR: OPTIONAL KITS

• Body Wraps








BODY SPECIFICATIONS

Below are the available station options for the Wire Event Container Series. With this measurement guide you will ensure the Wire Event Container is the right size to fit your space. The measurement guide is the essence of various standard measuring methods. The Wire Event Container is available in a Single configuration. Talk to your dedicated Busch Systems sales representative for more information on how to choose the right size container for your space.





Body Shape	Height	Width	Depth	Weight	Capacity
Wire Event Container™	30"H (762 mm)	20"W (508 mm)	15"D (381 mm)	18.9lbs (8.57 kg)	32 gal

STOCK BODY COLORS



Galvanized Steel



LID OPENING SPECIFICATIONS

The chart below outlines the available Lid Opening Options for each Wire Event Container™ as well as the associated opening dimensions. Be sure to run a preliminary audit of the popular materials that are discarded where your Wire Event Container™ will be placed. For example, if you're collecting large quantities of standard-sized Cans & Bottles, the Circle Opening is the ideal choice, as it will reduce contamination of materials that are larger than the dimensions of the opening. If there is a blank cell on the body or lid style of your choice, this means there is currently no stock option available. Talk to your dedicated Busch Systems® sales representative for more information.

	Full	Mixed	Slot	Circle	Solid-Lift	Vented-Lift
Wire Event Container™						摩 率
Opening Dimensions	11.125″W x 12.5″D	1.75"W x 11.25"D 5"W (circle)	1.75″W x 11.75″D	5.5" Diameter	7.5″W x 12.5″D	7.5″W x 12.5″D

STOCK LID COLORS



Blue



Green



Grey













PCR*

STOCK LABELS















































NOTE: Because different computers, monitors, and printers render colors and textures differently, actual finishes may vary from those shown here.

PCR* *Available in select lids only. Ask your sales representative for further details.

^{*}Grey represents clear. Clear will show color of lid. All other areas on labels are printed white.



IDEAL BAG SIZES

	Wire Event Container™
Ideal Bag Size (inches)	36 x 39

MATERIAL & CONSTRUCTION DETAILS

Not all recycling & waste receptacles are created equal. Our company policy is never to compromise on our workmanship or the quality material standards we've set. We only recommend and use quality first grade materials on our recycling & waste containers, and source these from OEM's at highly-competitive prices. Being a manufacturer that buys at high-quantities gives significant buying power with companies which in turn saves you money.

The design process, materials used, finishes and manufacturing standards all affect the final product. Every decision is vital to getting the most value for your investment. You deserve recycling & waste containers that meets your demands for quality and durability and will enhance your working environment for years to come.

Component	Material(s)	Construction
Body	Galvanized Steel	Sturdy construction
Lids	HDPE	Lids are molded from durable HDPE and contain up to 35% recycled content
PCR Lids	PCR PP	Lids are molded from durable 100% Post-Consumer Recycled Polypropylene.

ENVIRONMENTAL CONSIDERATIONS

- All Wire Event Container™ receptacles use a low energy, resource efficient manufacturing and curing process
- All Wire Event Container™ receptacle components disassemble at end of life and are fully recyclable
- Low maintenance and extremely long service life
- Manufactured in North America
- Product Carbon Footprint Dashboard for 1 Unit Wire Event Container™

Configurations	Post-Industrial	Post-Consumer	Total Recycled	3rd Party
	Recycled Content	Recycled Content	Content	Certifications
Wire Event Container™	Contact us	Contact us	Contact us	-

Busch Systems® is dedicated to environmental responsibility. We maintain an Environmental Management System and are continually working to improve our impact through efficiency, material selection, vendor education, employee involvement, and an unwavering commitment to being a B-Corporation®. If you would like additional information on our product development process or if you don't see the information you need for your project on this page, please contact our Sustainability Team at sustainability@buschsystems.com.



LEAD TIME

Our standard lead times on stock SKU's for the Wire Event Container™ Series are 3-5 days. Our standard lead times on large/custom orders for all Wire Event Container™ Series are 6-8 weeks. Please contact us to discuss your specific timing requirements.

PRICING

Please contact us at 800.565.9931 or sales@buschsystems.com. At Busch Systems®, we design, manufacture and sell our products directly to you. Our sales team is available to assist you with questions about our products, requests for quotes, and orders. Vertical Managers are located across North America to assist with the front-end specification and quoting process, and our in-house Project Sales Coordinators follow your project through from the time you place an order to shipment.

TO ORDER PLEASE SPECIFY

Quantity, body model, lid model, label choice and any optional product accessories. Talk to your dedicated Busch Systems® sales representative for more information. If you do not have a dedicated Sales Representative please contact us via our website at buschsystems.com/contact-us/

INSTALLATION

Busch Systems® Wire Event Container™ containers are hassle-free when it comes to installation. Each container is individually boxed using cardboard with high recycled content and each associated lid is boxed within the container box to ensure safe transport.

TO INSTALL YOUR Wire Event Container™:

- 1. Unbox the body and lid components
- 2. Insert the recycling/waste bag into the body and wrap the top edge of the bag around the body
- 3. Place the lid on top of the body

CARE & MAINTENANCE

Advantages of Busch Systems® HDPE & LDPE lids include:

- Great low temperature impact resistance and excellent chemical resistance
- Great high temperature impact resistance
- Lower stiffness rating which reduces potential for stress cracking
- High strength-to-density ratio

Their appearance and lifespan will be greatly affected by their care. The frequency of cleaning required depends on the environment in which the containers are used. Outdoor containers will be subject to different environmental conditions than indoor units, i.e. sun, rain, wind, pollution, winter temperatures, and salt/sea air.

To avoid the accumulation of dirt and grime on your Busch Systems® products, and help prevent corrosion, we recommend that a mild detergent be used (not an abrasive), such as a pH-neutral liquid (hand dishwashing or hand car washing soaps, for example) diluted in warm water. Wipe with a clean wet cloth and towel dry. Any dirt adhering to the powder coating should be removed. In order to remove deposits such as salt or dust, use a soft brush (non-abrasive). If this is not sufficient to remove stubborn soiling, the following products have been tested for use:

- Ajax Cream
- Flash (in water)
- Cutting compound ('T. Cut')

- Liquid Gumption
- Ajax Liquid (in water)

Note: Always test soaps/cleaners on a hidden and/or small area beforehand

If solvents are absolutely needed to remove marks, a soft cloth dampened with white spirit may be used.

GENERAL CARE

- Clean with a power washer or light scrub brush (outdoor/municipal bins)
- Clean with a mild detergent with damp sponge or cloth (indoor/office bins)
- · For soil and stain remover, cleaners like Fantastik, Armor All or Acetone may be tried
- UV safe cleaners MUST be used on all outdoor bins

THINGS TO AVOID

- Cleaners with chloride or bleach
- Abrasive detergents

Solvents

Steel wool or Scouring pads

Contact Us Today for a Quote on Your Wire Event Container™ Series Station!















