



## Juno® Trac-Lites™ Low Voltage Halogen Spotlights

Stylish, economical spotlights to complement any interior

**juno®**



## Juno<sup>®</sup> Trac-Lites<sup>™</sup> Low Voltage Halogen Spotlights

The perfect blend of form, function and value, Juno Trac-Lites is the system of choice. A wide variety of low voltage halogen spotlights are available to illuminate many of today's most stylish interiors. No matter what your application, you are sure to find the solutions you need at prices you can afford.



R741



R701



R702



R731



R740

## Juno® Low Voltage Halogen Spotlights MR16


**R741  
Cast Cube**



12V, 20-50W Halogen MR16

Complete unit includes a miniature 12V, 50VA solid state electronic transformer. Aiming locks help retain fixture position during relamping. Accepts one 2" accessory.

**Finishes:** White (WH), Black (BL),  
Satin Chrome (SC)




**R701  
Cylinder**



12V, 20-50W Halogen MR16

Complete unit includes 12V, 50VA solid state electronic transformer. Aiming lock helps retain fixture position during relamping. Accepts one 2" accessory.

**Finishes:** White (WH), Black (BL)




**R702  
Round Back**



12V, 20-50W Halogen MR16

With black bezel. Complete unit includes 12V, 50VA solid state electronic transformer. Accepts one 1-3/4" accessory.

**Finishes:** White (WH), Black (BL)




**R731  
Gimbal Ring**



12V, 20-50W Halogen MR16

Complete unit includes 12V, 50VA solid state electronic transformer. Aiming lock helps retain fixture position during relamping. Accepts one 2" accessory.

**Finishes:** White (WH), Black (BL)




**R740  
Pinchback**



12V, 20-50W Halogen MR16

Complete unit includes 12V, 50VA solid state electronic transformer. Aiming lock helps retain fixture position during relamping. Accepts one 2" accessory.

**Finishes:** White (WH), Black (BL)



All Trac-Lites™ low voltage fixtures are also compatible with Juno Trac-Master™



## Juno® Low Voltage Accessories

|                                                                                                                                                                           |  | 1 3/4"                          | Compatible With  | 2"               | Compatible With        |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|---------------------------------|------------------|------------------|------------------------|
| <b>Light Control Lenses</b><br>These alter the light distribution of a given lamp, enlarging or elongating it, softening the beam edge or removing striations.            |  | <b>Light Control Lenses</b>     |                  |                  |                        |
|                                                                                                                                                                           |  | Linear Spread Lens              | LSPREAD 175      | LSPREAD 200      | R701, R731, R740       |
|                                                                                                                                                                           |  | Prismatic Spread Lens           | PRISM 175        | PRISM 200        |                        |
|                                                                                                                                                                           |  | Uniformity Lens                 | SOLITE 175       | SOLITE 200       |                        |
|                                                                                                                                                                           |  | Diffusion Lens                  | DIFF 175         | DIFF 200         |                        |
| <b>UV Filters</b><br>These museum quality lenses filter out ultraviolet radiation below 400 nanometers to protect fade sensitive art and objects.                         |  | <b>UV Filter</b>                | UVF 175          | UVF 200          |                        |
|                                                                                                                                                                           |  |                                 |                  |                  |                        |
| <b>Color Correction Filters</b><br>Color Correction Filters correct the light, either to warm it up to approximate incandescent, or cool it down to approximate daylight. |  | <b>Color Correction Filters</b> |                  |                  |                        |
|                                                                                                                                                                           |  | Halogen-to-Incandescent, 2700K  | DCCF 175 HAL2700 | DCCF 200 HAL2700 |                        |
|                                                                                                                                                                           |  | Halogen-to-Daylight, 4250K      | DCCF 175 HAL4250 | DCCF 200 HAL4250 |                        |
| <b>Color Filters</b><br>These change white light into colored light and are available in colored glass and more efficient/saturated dichroic glass filters.               |  | <b>Colored Glass Filters</b>    |                  |                  |                        |
|                                                                                                                                                                           |  | Medium Pink                     | CGF 175 MPINK    | CGF 200 MPINK    | R701, R731, R740, R741 |
|                                                                                                                                                                           |  | Warm Red                        |                  | CGF 200 WRED     |                        |
|                                                                                                                                                                           |  | Daylight Blue                   |                  | CGF 200 DLTBLUE  |                        |
|                                                                                                                                                                           |  | Medium Blue                     | CGF 175 MBLU     | CGF 200 MBLU     |                        |
|                                                                                                                                                                           |  | Medium Amber                    | CGF 175 MAMB     | CGF 200 MAMB     |                        |
|                                                                                                                                                                           |  | Medium Green                    |                  | CGF 200 MGRN     |                        |
|                                                                                                                                                                           |  | <b>Dichroic Glass Filters</b>   |                  |                  |                        |
|                                                                                                                                                                           |  | Red                             | DGF 175 DRED     | DGF 200 DRED     |                        |
|                                                                                                                                                                           |  | Medium Green                    | DGF 175 MGRN     | DGF 200 MGRN     |                        |
|                                                                                                                                                                           |  | Medium Blue                     | DGF 175 MBLU     | DGF 200 MBLU     |                        |
|                                                                                                                                                                           |  | Yellow                          | DGF 175 DYEL     | DGF 200 DYEL     |                        |
|                                                                                                                                                                           |  | Magenta                         | DGF 175 MAGEN    | DGF 200 MAGEN    |                        |
|                                                                                                                                                                           |  | Blue Green (Cyan)               | DGF 175 CYAN     | DGF 200 CYAN     |                        |
| <b>Louvers</b><br>Hexcell louvers reduce perceived fixture brightness.                                                                                                    |  | <b>Hexcell Louver</b>           | HCLBL 175        | HCLBL 200        |                        |
|                                                                                                                                                                           |  |                                 |                  |                  |                        |

