

Why use copper press fittings?

Copper press utilizes a unique process which can eliminate the excess copper that normally accumulates in the pipe fittings. This allows water or gas to flow smoothly throughout the piping systems. By reducing the resistance within the system, this improves the performance of the overall system.

A more secure way for connection

Copper press fittings adopt a unique limit slot design. Compared to the traditional limit points, this design can effectively avoid product rupture and leakage when creating joints, so that customers can use the products more safely and securely.

Feature & Benefits

- Fully Certified
- Reliable and simple to use
- Secure and permanent joint
- Practical design
- Leak indicator
- Flame-free installation

Six simple steps to install



1 Cut the pipe to the length required



2 Remove any burrs left from cutting



3 Ensure O-rings are correctly in place



4 Mark the insertion depth



5 Ensure pipe is inserted fully to the stop



6 Press and finish

Copper Press fittings can be pressed with Milwaukee, REMS, Rigid and Rothenberger tools and associated CTS jaws. Contact Cello Products Customer Service for specific jaw set capability.

Compliant with

ASME B16.51

Uniform Plumbing Code (UPC)

International Plumbing Code (IPC)

Section 116875 of the California- Health & Safety Code

**NSF/ANSI/CAN 61-2022
Drinking Water System Components
Health Effects**

**NSF/ANSI/CAN 372-2022,
Drinking Water System Components
Lead Content**

**Building Materials Evaluation
Commission (Ontario)
Authorized – BMEC**



Press x Press 90° Elbow

Part ID	Size (inches)	Inner Qty	Carton Qty	Weight (lbs)
BP7-08	1/2	10	240	0.12
BP7-12	3/4	10	100	0.2
BP7-12-08	3/4 x 1/2	15	240	0.15
BP7-16	1	5	60	0.29
BP7-16-12	1 x 3/4	10	70	0.25
BP7-20	1 1/4	2	36	0.4
BP7-24	1 1/2	2	20	0.79
BP7-32	2	2	12	1.21
BP7-40	2 1/2	1	12	2.09
BP7-48	3	1	9	2.1
BP7-64	4	1	4	5.61




Press x Fitting 90° Elbow

Part ID	Size (inches)	Inner Qty	Carton Qty	Weight (lbs)
BP7-2-08	1/2	10	240	0.11
BP7-2-12	3/4	10	100	0.19
BP7-2-16	1	5	60	0.27
BP7-2-20	1 1/4	2	36	0.41
BP7-2-24	1 1/2	2	20	0.76
BP7-2-32	2	2	12	1.16
BP7-2-40	2 1/2	1	14	2.05
BP7-2-48	3	1	9	3.03
BP7-2-64	4	1	4	5.68



Press x Female IPS Drop Ear 90° Elbow

Part ID	Size (inches)	Inner Qty	Carton Qty	Weight (lbs)
BP735-08	1/2	10	80	0.29
BP735-12	3/4	8	64	0.43



Press x Press 45° Elbow

Part ID	Size (inches)	Inner Qty	Carton Qty	Weight (lbs)
BP6-08	1/2	10	240	0.1
BP6-12	3/4	10	120	0.16
BP6-16	1	5	60	0.22
BP6-20	1 1/4	4	40	0.31
BP6-24	1 1/2	2	24	0.6
BP6-32	2	2	12	0.87
BP6-40	2 1/2	1	16	1.74
BP6-48	3	1	12	2.27
BP6-64	4	1	6	4.1



Press x Fitting 45° Elbow

Part ID	Size (inches)	Inner Qty	Carton Qty	Weight (lbs)
BP6-2-08	1/2	10	240	0.09
BP6-2-12	3/4	10	120	0.15
BP6-2-16	1	10	60	0.21
BP6-2-20	1 1/4	4	40	0.3
BP6-2-24	1 1/2	2	20	0.58
BP6-2-32	2	2	12	0.84
BP6-2-40	2 1/2	1	16	1.56
BP6-2-48	3	1	12	2.32
BP6-2-64	4	1	6	3.95



Press x Press x Press Tee

Part ID	Size (inches)	Inner Qty	Carton Qty	Weight (lbs)
BPT-08	1/2	10	120	0.21
BPT-12	3/4	10	60	0.35
BPT-16	1	4	40	0.51
BPT-20	1 1/4	2	24	0.66
BPT-24	1 1/2	2	16	1.22
BPT-32	2	1	8	1.72
BPT-40	2 1/2	1	10	2.12
BPT-48	3	1	6	3
BPT-64	4	1	4	5.46